

External 192V 3U Rack/Tower Battery Pack for select Tripp Lite UPS Systems (BP192V12-3U)

MODEL NUMBER: **BP192V12-3U**



Description

Tripp Lite's BP192V12-3U rack/tower external battery pack offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Multi-use form factor supports configuration in rackmount or stacking applications using only 3 rack spaces (3U). Upright tower configuration supported with optional 2-9USTAND accessory. Includes heavy-gauge cabling with high-current DC connectors for simple installation. Additional output connector allows multiple BP192V12-3U battery packs to be daisy-chained to the UPS for even longer extended run operation.

COMPATIBLE UPS SYSTEMS - SU5000RT4U, SU6000RT4U, SU8000RT4U, and other Tripp Lite UPS systems that specify the use of this battery pack.

Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Supports stacking or rackmount installation using only 3 rack spaces (3U)
- Supports upright tower installation with optional 2-9USTAND accessory (holds 3 battery packs in tower configuration)
- Set of two input/output connectors allows multiple BP192V12-3U battery packs to be daisy-chained to the UPS for even longer extended run operation
- Includes heavy-gauge cabling with high-current DC connectors for simple installation

Highlights

- Extends the runtime of expandable 192V DC Tripp Lite UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount and tower installation available

Applications

- Ideal means of lengthening the battery runtime provided by compatible Tripp Lite UPS systems. Additional battery packs may be ordered at time of original UPS purchase or sourced at a later date to extend runtime performance if site power conditions deteriorate and longer battery runtime is desired.

Package Includes

- BP192V12-3U external battery pack
- Mounting hardware
- Warranty information
- Instruction manual

Specifications

General Info	
RoHS	Y
OUTPUT	
Overload Protection	50A DC output fuse



INPUT	
UPS Input Cord Length (ft.)	36 in./9m, 8 AWG, 3 conductor
UPS Input Cord Length (m)	10.97
BATTERY	
Expandable Battery Runtime	Includes a second input/output connector to daisy-chain multiple battery packs
DC System Voltage (VDC)	192
UPS Connection	Detachable cable with UPS specific DC connector (90 cm length, 8 gauge)
Typical Battery Lifespan	4-6 years typical (North America)
PHYSICAL	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM); Tower (2-9USTAND)
Shipping Dimensions (hwd / in.)	11.25 x 31.5 x 23
Shipping Dimensions (hwd / cm)	28.6 x 80 x 58.4
Shipping Weight (lbs.)	211.25
Shipping Weight (kg)	95.9
Unit Dimensions (hwd / in.)	5.25 x 17.5 x 28
Unit Dimensions (hwd / cm)	13.3 x 44.5 x 71.1
Unit Weight (lbs.)	174
Unit Weight (kg)	79
Material of Construction	Black steel cabinet
WARRANTY	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available