

## Cat5e 350MHz Molded Shielded Patch Cable (RJ45 M/M) - Gray, 50-ft.

MODEL NUMBER: **N105-050-GY**



### Highlights

- Protect your network data from EMI/RFI interference
- Molded boot provides extra strain-relief and durability

### Package Includes

- 50ft Gray Cat5e Shielded Patch Cable

### Description

Protect your high-speed network from noise and electromagnetic interference with Tripp Lite's 50-ft. gray, Category 5e (Cat5e) Shielded patch cable. This cable features 2 shielded RJ45 Gold molded male connectors with integral strain relief. The cable is manufactured from PVC, 4-pair, stranded shielded twisted pair, and is rated for 350MHz/1Gbps communication.

### Features

- Provides EMI/RFI shielding in Ethernet networks
- Shielded RJ45 connectors with gold-plated contacts
- 4-pair 24 AWG Stranded STP with drain wire
- Molded boot for extra strain-relief and durability
- TSB 568B (AT&T 258A) Wiring
- TIA/EIA and UL Certified

## Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Cat5/5e
Model Type	Shielded
Cable Types	CAT5/CAT5E
INPUT	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Cable Length (ft.)	50
Cable Length (m)	15.24
<b>PHYSICAL</b>	
Color	Gray
<b>CONNECTIONS</b>	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE)
Number of Connectors	2
<b>CERTIFICATIONS</b>	
Certifications	RoHS-Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.