

## Universal AC Power Adapter Cord, 13A, 16AWG (IEC-320-C14 to NEMA 5-15R), 2-ft.

MODEL NUMBER: **P002-002**



### Description

The P002-002 Power Cord is 2-ft. AC Power Adapter Cord that allows you to plug a NEMA 5-15P power cord into an IEC-320-C13 outlet on a PDU or UPS. Features a NEMA 5-15R receptacle (female) with an IEC-320-C14 plug (male). The P002-002 is manufactured using superior materials, and is UL listed. The P002-002 is backed by a lifetime warranty.

### Features

- UL Listed
- Allows you to plug a power cord with an NEMA 5-15P into an IEC-320-C13 outlet in a PDU or UPS.
- Frees up a wall outlet
- Plug type: IEC-320-C14 (CPU) to NEMA 5-15R
- 16AWG SJT, 13A, 125V

## Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	2

### Highlights

- Allows you to plug a NEMA 5-15P power cord into an IEC-320-C13 outlet in a PDU or UPS.
- 2-ft. power cord rated at 13A, 125V
- Connectors: Male IEC-320-C14 / Female NEMA 5-15R
- UL Listed

### System Requirements

- A monitor with an AC power cord (NEMA 5-15P)
- A computer with an available power receptacle (IEC-320-C13)

### Package Includes

- 2-ft. AC power adapter cord PC style male (IEC-320-C14) to AC female (NEMA 5-15R)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Cable Length (m)	0.61
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	IEC-320-C14
Connector B	NEMA 5-15R
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.