

Standard Computer Power Extension Cord, 10A, 18AWG (IEC-320-C14 to Left Angle IEC-320-C13), 2-ft.

MODEL NUMBER: P004-002-13LA



Highlights

- C13 Left Angle - C14
- 18AWG (0.824mm), SJT, 10A, 100-250V

Package Includes

- 2-ft. universal AC power extension PC style male (IEC-320-C14), to PC style female (IEC-320-C13), Left Angle

Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This handy 2ft. cord can be used to extend the power cord on any PC or device with a C14 plug. Features an IEC-320-C14 to IEC-320-C13 Left Angle exit connection.

Features

- 2-ft. power extension cord for your PC or device with a C14 plug
- Plug type: IEC-320-C14 (male) to IEC-320-C13 Left Angle (female)
- 18AWG (0.824mm), SJT, 10A, 100-250V

Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.61



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	IEC-320-C14
Connector B	IEC-320-C13 - LEFT ANGLE
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.