

## Standard Computer Power Extension Cord, 10A, 18AWG (IEC-320-C14 to Right Angle IEC-320-C13), 2-ft.

MODEL NUMBER: **P004-002-13RA**



### Highlights

- UL Listed
- C13 Right Angle - C14
- 18AWG (0.824mm), SJT, 10A, 100-250V

### Package Includes

- 2-ft. universal AC power extension PC style male (IEC-320-C14) to PC style female (IEC-320-C13) Right Angle

### Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This handy 2ft. cord can be used to extend the power cord on any PC or device with a C14 plug. Features an IEC-320-C14 to IEC-320-C13 Right Angle connection. UL listed.

### Features

- UL Listed
- 2-ft. power extension cord for your PC or device with a C14 plug
- Plug type: IEC-320-C14 (male), to IEC-320-C13 (female) Right Angle
- 18AWG (0.824mm), SJT, 10A, 100-250V

## Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	2



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Cable Length (m)	0.61
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	IEC-320-C14
Connector B	IEC-320-C13 - RIGHT ANGLE
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.