

## Heavy-Duty Power Extension Cord, 15A, 14AWG (IEC-320-C14 to IEC-320-C13), 6-ft.

MODEL NUMBER: P005-006



### Highlights

- C13 to C14 Power Cable, 6 ft.
- 14 AWG x 3C
- 15A / 100 - 250V
- RoHS Compliant
- UL Listed

### Package Includes

C13 to C14 Power Cable, 6 ft.

### Description

Use Tripp Lite's P005-006 in server applications that require a higher rated, heavier gauge cable. C13 to C14 connectors, 3 x 14 AWG conductors, 15A rating, 100-250V.

### Features

- Molded, Heavy-Duty Power Cable, 6 ft.
- IEC-60320-C13 to IEC-60320-C14
- 14 AWG x 3C, SJT, 15A, 100-250 Volt
- RoHS Compliant
- UL Listed

## Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	6



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Cable Length (m)	1.83
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	IEC-320-C14
Connector B	IEC-320-C13
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.