

Heavy-Duty Power Extension Cord Y Splitter Cable, 30A, 10AWG (NEMA L6-30P to 2x NEMA L6-30R), 1-ft.

MODEL NUMBER: P041-001-2



Highlights

- L6-30P to 2 x L6-30R Power Splitter
- 10AWG x 3C, 30-Amp
- RoHS Compliant

Package Includes

- 1-ft. L6-30P to 2 x L6-30R Power Splitter Cable

Description

Tripp Lite's Power Splitter Cable - L6-30P male to 2 x L6-30R female. Constructed with 3 x 10AWG copper conductors, fully molded ends and 250V/30A rating.

Features

- Molded, Heavy-Duty Power Splitter Cable, 1ft.
- NEMA L6-30P to 2 x NEMA L6-30R
- 10AWG x 3C, SJT, 30A, 250Volt
- RoHS Compliant

Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	NEMA L6-30P
Connector B	NEMA L6-30R (X2)
Number of Connectors	3
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.