

Heavy-Duty Power Extension Cord, 15A, 14AWG (IEC-320-C19 to IEC-320-C14), 2-ft.

MODEL NUMBER: P047-002



Highlights

- C19 to C14 Power Cable, 2 ft.
- 14 AWG x 3C, 15A , 100-250V
- RoHS Compliant

Package Includes

- C19 to C14 Power Cable, 2 ft.

Description

Tripp Lite Heavy Duty C19 to C14, 2 ft. Power Cable. Constructed with 3 x 14 AWG copper conductors, fully molded ends, 100-250V / 15A rating.

Features

- Molded, Heavy-Duty Power Cable, 2ft.
- IEC-60320-C19 to IEC-60320-C14
- 14 AWG x 3C, SJT, 15A, 100-250 Volt
- RoHS Compliant

Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.61



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	IEC-320-C14
Connector B	IEC-320-C19
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.