

Heavy-Duty Power Extension Cord, 20A, 12AWG (IEC-320-C19 to NEMA 5-20P), 10-ft.

MODEL NUMBER: P049-010



Highlights

- C19 to 5-20P Power Cable, 10 ft.
- 12 AWG x 3C
- RoHS Compliant

Package Includes

- C19 to 5-20P Power Cable, 10 ft.

Description

Tripp Lite Heavy-Duty C19 to 5-20P 10 ft. Power Cable. Constructed with 3 x 12 AWG copper conductors, fully molded ends, 125V/20A rating.

Features

- Molded, Heavy-Duty Power Cable, 10 ft.
- IEC-60320-C19 to NEMA 5-20P
- 12 AWG x 3C, SJT, 20A, 125 Volt
- RoHS Compliant

Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.05



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	NEMA 5-20P
Connector B	IEC-320-C19
Number of Connectors	2
CERTIFICATIONS	
Approvals	UL-approved
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.