

Mini DisplayPort to DisplayPort Cable Adapter, Video Converter, 2560x1600 (M/F)

MODEL NUMBER: P139-06N-DP



Highlights

- Converts Mini Displayport on a MAC to Displayport Female
- Connect Displayport enabled monitor to a MAC computer
- Supports resolutions up to 2560 x 1600 @ 60Hz

Package Includes

6-inch Mini Displayport Male to Displayport Female Adapter

Description

Tripp Lite P139-06N-DP converts a Mini-Displayport video out port on a MAC, or other computer, to Displayport, allowing attachment of a Displayport monitor or HDTV with Displayport input. Plug the adapter into the computer, and then a standard Displayport cable from the adapter to the monitor.

Features

- Connect a Displayport enabled Monitor to a MAC Mini-Displayport video port
- Plug and Play - no drivers or setup needed
- Displayport 1.1a Compliant
- HDCP Compliant
- Supports resolutions up to 2560 x 1600 @ 60Hz

Specifications

General Info	
RoHS	Y
OVERVIEW	
Chromebook Compatible	No
Display Style	Adapter
Model Type	DisplayPort
Cable Types	DISPLAYPORT
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	0.5
PHYSICAL	
Color	White
CONNECTIONS	
Connector A	MINI DISPLAYPORT (MALE)
Connector B	DISPLAYPORT (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.