


# SmartRack 12U Hinged Wall-Mount Standard-Depth Rack Enclosure Cabinet

MODEL NUMBER: **SRW12US**



### Highlights

- 12U with adjustable front and rear vertical rackmount rails
- Hinged cabinet swings away from wall bracket for easy equipment access (swing direction is reversible)
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance
- Interior vertical posts have square holes for cage nuts plus 12-24 threaded mounting holes

### Description

Tripp Lite's SRW12US Wall Mount Rack Enclosure Cabinet is the ideal storage solution for standard rackmount equipment in applications with limited floor space. Constructed with a hinged wall mounting bracket and a sturdy steel frame, it can accommodate up to 200 lbs. of equipment in 12U of rack space. Four adjustable vertical mounting rails with square holes accommodate all standard 19-inch rack equipment. To allow easy access to rackmounted equipment, the enclosure cabinet is hinged to swing away from the wall mounting bracket. The SRW12US also features perforated lockable side panels and front door, assuring generous airflow to keep equipment operating safely. The front door is reversible and the side panels are removable for easy access to equipment. The top and bottom panels of the enclosure include convenient cable routing ports.

### Features

- 12U wall-mounted enclosure
- Adjustable mounting depths from 3" to 20.5" inches
- Ventilated front door and side panels for increased airflow
- Hinged cabinet swings away from wall bracket for easy equipment and cable access
- Locking, reversible front door
- Locking, removable side panels
- Top and bottom panel cable access openings
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

### Package Includes

- SRW12US Wallmount Rack Enclosure
- (20) M6 screws
- (20) M6 cage nuts
- (20) M6 washers
- (2) Keys
- Owner's Manual

## Specifications

General Info	
RoHS	Y



OVERVIEW	
Style	Wall Mounted
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	20.5
Installed Whole System Maximum Rack Depth (cm)	52.07
Installed Whole System Minimum Rack Depth (in.)	3
Installed Whole System Minimum Rack Depth (cm)	7.62
Rack Height (U Spaces)	12
Shipping Dimensions (hwd / in.)	27.95 x 26.38 x 24.41
Shipping Dimensions (hwd / cm)	70.93 x 67 x 62
Shipping Weight (lbs.)	64
Shipping Weight (kg)	28.8
Unit Dimensions (hwd / in.)	25 x 23.63 x 21.6
Unit Weight (lbs.)	60
Unit Weight (kg)	27.21
Unit Dimensions (cm)	EXTERNAL DIMENSIONS: 63.5 x 60 x 54.9 (HWD)
Color	Black
Weight Capacity - Stationary (lbs.)	200
Weight Capacity - Stationary (kg)	90.7
Factory Preset Rack Depth (in.)	10.42
Factory Preset Rack Depth (cm)	26.47
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Hinged (Swings Away from Wall Bracket)	Yes
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-E, IEC 60297-3-100, DIN 41494, IP20 Protection Rating, RoHS



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.