


3U EUROCARD PLUGBOARD™ PART NO. : 4614-4

Description :

- 3U x 160mm, Hole Dia.: 0.055" & 0.042"(holes for DIN connector & buses), Grid: 0.100" x 0.100"
- Pad-Per-Hole
- Voltage and ground buses around board perimeter on both sides
- For solder, Wire-Wrap or mixed wiring methods
- Pad and bus surfaces solder-coated for user convenience
- Plated-thru holes
- Row and column legends pro-vided
- Layout paper..... [Layout Paper\(PDF\)](#)



Circuit Pattern :	Pad-Per-Hole
16 Pin DIP Capacity :	30
Hole Diameter :	0.055" { 1.397 mm }, 0.042" { 1.0668 mm }
Grid :	0.100" x 0.100" { 2.54mm X 2.54mm }
Dimension { H, W, T } :	3.94" x 6.30" x 0.062" -----> { 3U x 160mm }
Material :	FR4 Epoxy Glass { MIL - P13949 type Gf }
Wire-Wrap Terminals :	T44, T46, T49 & T68
96 Pin DIN Connector :	RE96MWR { Available Separately }
Wire-Wrap Socket Pins :	R32
Recommended Card Cage:	CCK160-3U Series Card Cage { Subracks }
NEMA Grade :	FR4
UL Flammability Class :	94V - 0