

Lite Duty Caster Set *1425P Series*

Features



- Twin nylon swivel wheels with zinc axles and hoods.
- 5/16 - 18 threaded stem mounts into existing holes in base of rack (in place of leveling feet).
- Final mounting height of 2.75" (70 mm).
- Features zinc plated ball bearing pivot, composite wheels.

Compatibility

- RCHS/RCHV
- RCSC
- REFK
- DNRRHDW
- RS
- 1564



Part No.	Strength	Wheel Diameter	Overall Height		Caster Set Weight Capacity	Caster Set Quantity		Physical Wheel Weight
			Added to Cabinet			Included In Set	Brakes Included	
1425P	Lite Duty	2.37	2.75		400	4	No	3 lb (1.4 kg)

Data subject to change without notice