

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130057-0001](#)
Status: **Active**
Overview: Brad® Industrial Ethernet Solutions
Description: Brad® RJ-Lnxx™, Threaded, RJ-45 Ethernet Field-Attachable Connector for Standard Core Cable

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|----------------|---|
| Product Family | Field Attachable / Accessories |
| Series | 130057 |
| IP Rating | IP67 |
| Overview | Brad® Industrial Ethernet Solutions |
| Product Name | Brad®, RJ-Lnxx® |
| Type | Field Attachable Connector |
| UPC | 78678848445 |

Physical

| | |
|-------------------------------|-----------------|
| Cable Diameter | N/A |
| Coupling Type | Internal Thread |
| Diagnostics / LEDs | No |
| Diagnostics Port | No |
| Gender | Male |
| Keyway | None |
| Material - Connector Body | Polycarbonate |
| Material - Contact | Copper |
| Material - Coupling Nut | ABS |
| Material - Plating Mating | n/a |
| Net Weight | 22.960/g |
| Orientation | Straight |
| Poles | N/A |
| Temperature Range - Operating | -20°C to +80°C |
| Wire Size AWG | N/A |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 250V |

Material Info

| | |
|-----------------|----------|
| Old Part Number | ENQAM315 |
|-----------------|----------|

Reference - Drawing Numbers

| | |
|---------------|---------------|
| Sales Drawing | SD-130057-001 |
|---------------|---------------|




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130057Series