



# E2270SWN

## 54.6cm (21.5") LCD MONITOR

For work or home, this monitor offers excellent performance with 16.7 million colors and 5ms response time. Smart features like Eco Mode and e-Saver help you effortlessly reduce power consumption.



SCREEN+



VESA



E-SAVER



I-CARE



TILT

### GENERAL FEATURES

Line	Value-line
Panel Type	TN
Panel Size	21.5" / 54.6 cm
Aspect Ratio	16:9
Brightness	200 cd/m <sup>2</sup>
Contrast Ratio Dynamic	20M:1
Pixel Pitch(H) (V)	0.248
Display Area (H x V)	476.64x268.11
Viewing Angle (CR >= 10)	90/65
Response time	5ms
Color	Black

### SCANNING FREQUENCY

Scanning Frequency	30-83khz/50-76hz
Pixel Frequency	108Mhz

### RESOLUTION

Maximum Resolution	1920x1080@60Hz
Recommended Resolution	1920x1080@60Hz
HDCP compatible	-

### CONNECTORS

D-Sub	Yes
DVI	-
HDMI	-
USB	-
MHL	-
DisplayPort	-

### POWER

Power Source	100 - 240V 50/60Hz
Power Consumption	On: 14,8W, Standby: 0,29W, Off: 0,24W
Zero Power Switch	-

### OTHER FEATURES

Plug and Play	Yes
User Control	Button
Headphone Out	-
Height Adjustment	-
Pivot	-
Swivel	-
Tilt	-5/+15

Regulations	Energystar 6 TCO no EPEAT Silver TUV-GS TUV-Bauart CE FCC EAC RoHS compliant
-------------	--

Specific Features	iCare i-Menu e-Saver Screen+ Vesa Wallmount
-------------------	---

### ACCESSORIES

VGA Cable
Power Schuko C7 Cable

### DIMENSIONS

Product with stand (W×H×D)	503,37x47,98x311,1 mm
Packaging (W×H×D)	560x395x110 mm
Weight	2.7 kg wo/packaging 3.45 kg w/packaging
Warranty	3 Years
EAN	4038986123891