


T-1 3/4 Midget Flange Base



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
331	1.35	.060	.010	500	C-6
268	2.50	.350	.200	10,000	C-2R
343	2.50	.400	.550	30	C-2R
368	2.50	.200	.220	500	C-2R
338	2.70	.060	.040	6,000	C-2R
375	3.00	.015	.004	10,000	C-6
8848	3.00	.350	.300	10,000	C-2R
7331	4.50	.120	.050	25,000	C-2R
3150	5.00	.060	.150	5,000	C-2R
7332	5.00	.060	.030	60,000	C-2R
7333	5.00	.060	.050	25,000	C-2R
7334	5.00	.190	.450	1,000	C-2R
7335	5.00	.115	.150	40,000	C-2R
328	6.00	.200	.600*	1,000	C-2R
345	6.00	.040	.030	10,000	C-2V
7336	6.00	.200	.100	50,000	C-2F
349	6.30	.200	.550	5,000	C-2R
350	6.30	.150	.450	3,000	C-2R
377	6.30	.075	.230	1,000	C-2R
380	6.30	.040	.020	20,000	C-2V
381	6.30	.200	.400	20,000	C-2F
344	10.0	.014	.002	50,000	C-2F
367	10.0	.040	.080	5,000	C-2F
7338	11.0	.022	.030	10,000	C-2F
394	12.0	.040	.120	10,000	C-2F
330	14.0	.080	.500	1,500	C-2F
382	14.0	.080	.300	15,000	C-2F
8918	14.0	.100	.500	10,000	C-2F
370	18.0	.040	.150	10,000	C-2F
459	22.0	.040	.300	2,000	C-2F
8176	24.0	.050	.500	1,000	C-2F
327	28.0	.040	.340	4,000	C-2F
376	28.0	.060	.340	25,000	C-2F
385	28.0	.040	.150	10,000	C-2F
387	28.0	.040	.300	7,000	C-2F
6034	28.0	.024	.150	4,000	CC-2F
7341	28.0	.065	.650	5,000	C-2F
269	32.0	.040	.300	4,000	C-2F
6848	48.0	.025	.200	5,000	CC-2F

* Lamp MSCP is .340 @ 5.0V