



S-11 Double Contact Bayonet Base




Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
1724	6.2	4.50	32.0	400	C-6
310	28.0	.90	32.0	300	C-2V
312	28.0	1.29	50.0	300	C-2V

T-3/4 Wire Terminal



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
7101	1.5	.015	.010	5,000	C-2R
28	4.5	.021	.020	5,000	C-2R
30	4.5	.021	.020	5,000	C-2R
3102	4.5	.022	.020	5,000	C-2R
2	5.0	.021	.030	10,000	C-2R
6153	5.0	.060	.150	3,000	C-2R
6803	5.0	.060	.030	60,000	C-2R
6833	5.0	.060	.050	25,000	C-2R
7102	5.0	.115	.200	5,000	C-2R
7133	5.0	.075	.090	25,000	C-2R
7153	5.0	.115	.150	40,000	C-2R
8537	5.0	.015	.020	1,000	C-2R
8666	5.0	.080	.150	15,000	C-2R

T-3/4 Micro-Midget Flange Base



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
3810	1.5	.015	.003	10,000	C-6
3811	1.5	.015	.010	5,000	C-6
7121	2.5	.110	.001	10,000	C-2R
6183	5.0	.060	.150	3,000	C-2
7122	5.0	.021	.030	10,000	C-2R
7123	5.0	.115	.200	5,000	C-2R
8270	5.0	.115	.150	40,000	C-2R