

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [88741-8120](#)
Status: **Active**
Overview: [MicroCross™ DVI Connectors and Cable Assemblies](#)
Description: MicroCross™ DVI Digital Visual Interface, Shielded I/O Cable Assembly: DVI-Digital-to-DVI-Digital, Dual Link TMDS, Black, 5.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	88744
Assembly Configuration	Dual Ended Connectors
Comments	Dual Link TMDS
Connector to Connector	DVI-Digital-to-DVI-Digital
Overview	MicroCross™ DVI Connectors and Cable Assemblies
Product Name	MicroCross™DVI
UPC	800754803298

Physical

Cable Length	5.0m
Circuits (Loaded)	24
Color - Resin	Black
Gender	Plug/Plug
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	537.120/g
Packaging Type	Bag
Pitch - Mating Interface	1.90mm
Plating min - Mating	0.254µm
Plating min - Termination	3.810µm
Single Ended	No
Termination Interface: Style	Solder or Weld
Wire Insulation Diameter	N/A
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	3.0A
Shielded	Yes

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-88741-002
---------------	--------------




image - Reference only

EU RoHS

RoHS Compliant by Exemption
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[88744Series](#)

Mates With

[74320 MicroCross™ DVI-I Digital/Analog Visual Interface, PCB Receptacle](#)