

Economy Wall Mount Rack *WMC Series*

Available while supplies last

X **Note:** This product line has been discontinued as a stocked series. Information is for reference only. It has been replaced with **RB-FW Series**. For alternative solution assistance, please contact Hammond Customer Service - sales@hammfg.com or USA (716) 630-7030, Canada and International (519) 822-2960.



RACK BASICS®



Looking for a deal? There are WMC products in our Clearance Section. [Click here to learn more.](#)

Features

- Constructed in light duty 16-gauge steel.
- Includes two (2) pairs of EIA-310-D compliant 19 inch square hole mounting rails.
 - Starter pack of M5 screws and cage nuts included.
 - For 10-32 hardware see the **1421CNABK Series**.
- Rails are adjustable in depth in 25mm increments.
- Tempered glass front door opens a full 180°.
- Front and sides vented for air flow.
- Removable side panels can be locked using optional key lock **SWCCLOC**.
- Rear cable access.
- Provision for optional fans on top panel.
- Ships unassembled - some assembly required.
- Finished in smooth black powder paint.
- Tested to nearly double the suggested load rating of 80 lbs.
- RoHS Compliant.

Part of the Rack Basics® line of economy rack solutions.

Accessories

- Horizontal Ring Cable Manager
- Grill Fan Kits
- Cable Lacing Bar
- Horizontal Lacing Strip
- Universal Rack Shelf
- Outlet Strips
- Mounting Hardware

Part No.	Overall Dimensions			Mounting Dimensions			Usable Depth	Rack Units	Replaced by Part No.
	Height	Width	Depth	Height	Width	Depth			
WMC1901023BK2	14.17	23.60	23.70	10.50	19.00	16.93	22.87	6U	RB-FW6
WMC1901523BK2	19.43	23.60	23.70	15.75	19.00	16.93	22.87	9U	RB-FW9
WMC1902123BK2	24.69	23.60	23.70	21.00	19.00	16.93	22.87	12U	RB-FW12
WMC1902623BK2	29.95	23.60	23.70	26.25	19.00	16.93	22.87	15U	RB-FW15

Lock for Side Panels

Part No.	SWCCLOC
----------	---------

Data subject to change without notice

© 2015. Hammond Manufacturing Ltd. All rights reserved.