

Welded Steel 2-Post Robust Rack *DNRRLDW Series*

Front 10-32 Tapped Rails



When strength and reliability is the highest priority, be sure to choose the Data/Networking Robust Rack (DNRR) from Hammond Manufacturing. Designed to support your rack mount infrastructure, regardless of the application, the DNRR includes premium features not found on most other racks.

Features

- Constructed in 12-gauge steel..
- Tested to nearly double the suggested load rating of 850 lbs, Hammond engineered the DNRR**LDW to exceed your weight requirements.
- Our automated tapping assembly provides EIA-310-D compliant 10-32 tapped rails on the front to ensure ease of mounting rack mount equipment.
- To keep the rack upright when loaded with equipment, we've included a large base for freestanding support. Optionally, the base can be caster mounted for moving the rack.
- To keep it looking great, the DNRR undergoes a three-stage paint process which includes a coat of premium smooth black powder paint.
- Before sending the DNRR on its way we cover the rails and base with a thick layer of cardboard to prevent any damage that may occur during transportation.
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Top Wire Management
- Two Post Mounting Adjustable Shelf
- Two Post Centered Shelf
- Adjustable Depth DIN Rail Panel
- Outlet Strips
- 10-32 Black Rack Screw with Nylon Washer
- 10-32 Rack Screws with Pilot Point
- Grounding
- Rack Unit Label
- Rack and Cabinet Baying/Ganging/Joining Kit
- Universal Rack Shelf
- Two Post Mounting Clamping Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- Hinged Acrylic Door Panel Cover
- Cable Management
- 10-32 Countersunk Rack Screw with Plastic Cup Washer
- Small Head 10-32 Thumb Screw
- Rack Panels
- Caster Set

Part No.	Overall Dimensions			Mounting Dimensions			Shipping
	Height	Width	Depth	Height	Width	Rack Units	Weight
DNRR42LDW	44.60	20.00	19.78	42.00	19.00	24U	38
DNRR63LDW	65.60	20.00	19.78	63.00	19.00	36U	41

Part No.	Overall Dimensions			Mounting Dimensions			Shipping
	Height	Width	Depth	Height	Width	Rack Units	Weight
DNRR70LDW	72.60	20.00	19.78	70.00	19.00	40U	42
DNRR77LDW	79.60	20.00	19.78	77.00	19.00	44U	45
DNRR84LDW	86.60	20.00	19.78	84.00	19.00	48U	47

Data subject to change without notice

© 2015. Hammond Manufacturing Ltd. All rights reserved.