

Pocket Light Meter

Technical Specifications

Range 0 to 200,000 Lux/20,000FC

Resolution 0.1/1/10/100

Accuracy $\pm 3\%$ of reading, $\pm 0.5\%$ below 10,000 Lux/FC
 $\pm 4\%$ of reading, ± 10 dgts above 10,000 Lux/FC

Power 1 x 9V PP3 Alkaline Battery

Dimensions 172 x 55 x 38mm

Weight 88g