

## **Splash-Proof Pen-Type Thermometer**

### **Technical Specifications**

|                   |   |
|-------------------|---|
| <b>Range</b>      | -50° to 300°C.                            |
| <b>Resolution</b> | 0.1°C                                     |
| <b>Accuracy</b>   | ±1°C (-30° to +150°C), ±2° (others)       |
| <b>Sampling</b>   | Every second                              |
| <b>Power</b>      | 1 x 3V Lithium Battery                    |
| <b>Dimensions</b> | 248 x 23 x 13mm (Unit) 150 x 4mmØ (Probe) |
| <b>Weight</b>     | 40g                                       |