

## Hi-Accuracy Dual Input K & J Type Thermometer

### Technical Specifications

<b>Range</b>	-200° to +1372°C, -328° to 2498°F Type K -200° to +1100°C, -328° to 2012°F Type J
<b>Resolution</b>	0.1° <1000°. 1° >1000
<b>Accuracy</b>	±(0.5%rdg +2°C) (<0°C) & (>1000°C) ±(0.15%rdg +1°C) (0 to 1000°C)
<b>Power</b>	1 x 9V PP3 Alkaline Battery
<b>Dimensions</b>	185 x 66 x 33mm
<b>Weight</b>	245g