

Pen Type Infrared Thermometer

Technical Specifications

Range -50° to +260°C (-58° to +500°F)

Resolution 0.1°C/°F

Accuracy ±2% of reading or ±2°C (-10° to +230°C), ±4°C (-10° to -50°C)

Power 2 x 1.5V Button Cell Batteries

Dimensions 88 x 19 x 23.3mm

Weight 33g