

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [84525-0017](#)
Status: **Active**
Overview: XRC™ (Extra Rugged Circular) Sealed Plugs and Receptacles
Description: XRC™ Female (Socket) Terminal, 14 to 18 AWG, Terminal Size 16, Insulation Diameter 1.91 to 3.30mm , Nickel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-84501-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	84525
Application	Power
Crimp Quality Equipment	Yes
Overview	XRC™ (Extra Rugged Circular) Sealed Plugs and Receptacles
Product Name	XRC™
UPC	78172511504

Physical

Gender	Socket
Material - Metal	Copper Alloy
Material - Plating Mating	Nickel
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.41-3.81mm
Wire Size AWG	14, 16, 18
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Product Specification	PS-84501-001
Sales Drawing	SD-84525-005



EU RoHS

ELV and RoHS Compliant
REACH SVHC
 Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[84525Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for 4.64mm Crimp Terminal, Pin	0638115600
FineAdjust™ Applicator for XRC™ Sealed Pin and Socket Crimp Terminals	0638679200
FineAdjust™ Applicator for XRC™ Sealed Terminal Pin and Socket Crimp Terminals	0638679000

This document was generated on 02/04/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION