


## Cylinder Type Polyacene Capacitors

PAS1235LA3R0206



## ■ Features

- Item Summary  
3.0 V, 20F±20%, Less than 0.1 Ω
- Lifecycle Stage  
Mass Production

## ■ Products characteristics table

Temperature Range	-25 to +60°C
Maximum Usable Voltage	3.0 V
Nominal Capacity	20F
Internal Resistance	0.1 Ω
Initial Capacitance	20F±20%
Initial Internal Resistance	Less than 0.1 Ω
RoHS Compliance	Yes
Soldering Method	Wave

2013.08.20

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
 Before making final selection, please check product specification.