




DS-301 Set

Dual Tone 25 Watt Siren with Enclosure
Sku: 4111136416



Features:

- Dual tone siren - steady and warble
- Stainless steel enclosure
- Indoor/outdoor use
- Dual tamper switches, front and rear
- Mounting hole for optional STL-1 strobe (shown)

Specifications:

Operating voltage:	6 - 14 VDC
Sound output:	117 dB @ 12 VDC
Current draw:	1 A @ 12 VDC
Dimensions:	5.7
Color:	White (siren), Stainless (box)
Material:	Stainless steel box and hardware with UV-resistant high impact plastic siren
Wiring:	Red-warble, Yellow-steady, White-common