


LOW VOLTAGE TEST LEADSFor 17th Edition Testing**Test probes**

**1001-991**


3 wire test lead set (1.4m)

Includes: 4mm plug leads (red, blue and green), croc clips and probes to GS38 (red, blue and green), plus extended probes for testing in deep terminals (red and blue).**Recommended for use with:**

MFT1700 series, MFT1800 series

Also compatible with:

MFT1500 series

**1001-975**

Fused 3 wire test lead set (1.4m)

Includes: 10 A fused 4mm plug leads (red, blue and green), croc clips and probes to GS38 (red, blue and green), plus extended probes for testing in deep terminals (red and blue).**Recommended for use with:**

MFT1700 series, MFT1800 series

Also compatible with:

MFT1500 series

**1005-135**

3 wire test lead set (1.3m)

Includes: 4mm plug leads (red, blue and green), croc clips and probes to GS38 (red, blue and green).**Recommended for use with:**

MFT1500 series

Also compatible with:

MFT1700 series, MFT1800 series

**1001-883**

3 wire test lead set (1.4m)

Includes: 3 leads (red, black and green) splitting out from special 3 pin Megger plug, croc clips and probes to GS38 (red, black and green).

Recommended for use with:

MFT1500 series, LRCD200 series, LT310/320/330, CM400, CM300, LT7

Also compatible with:

RCDT300 series

**1001-876**

3 wire test lead set (1.4m)

Includes: 3 leads (red, black and green) splitting out from special 5 pin Megger plug, croc clips and probes to GS38 (red, black and green).

Recommended for use with:

CM500, CM400/2, CM300/2, BMM2000 series, LCB2000 series

**1001-874**

2 wire test lead set (1.5m)

Includes: 2 leads (red and black) splitting out from special 5 pin Megger plug, croc clips and probes to GS38 (red and black)

Recommended for use with:

CM500, CM400/2, CM300/2, BMM2000 series


**1001-875**

2 wire test lead set (5m)

Includes: 2 leads (red and black) splitting out from special 5 pin Megger plug, croc clips and probes to GS38 (red and black)

Recommended for use with:

CM500, CM400/2, CM300/2, BMM2000 series

**1002-001**

2 wire test lead set (1.4m)

Includes: 4mm plug leads (red and black), croc clips and probes to GS38 (red and black), plus extended probes for testing in deep terminals (red and black).

Recommended for use with:

MIT200 series, MIT300 series, MIT400 series, AVO300 series, AVO410, DCM300 series

**1002-015**

Fused 2 wire test lead set (1.5m)

Includes: 500 mA fused 4mm plug leads (red and black), croc clips and probes to GS38 (red and black), plus extended probes for testing in deep terminals (red and black).

Recommended for use with:

MIT200 series, MIT300 series, MIT400 series, AVO300 series, AVO410, DCM300 series


**1001-976**

2 wire test lead set (1.4m)

Includes: 4mm plug leads (red and green), croc clips and probes to GS38 (red and green), plus extended probes for testing in deep terminals (red and green).

Recommended for use with:

LTW300 series, LTW425, LT300, RCdT300 series, LRCD200 series

**1001-977**

Fused 2 wire test lead set (1.5m)

Includes: 10 A fused 4mm plug leads (red and green), croc clips and probes to GS38 (red and green), plus extended probes for testing in deep terminals (red and green).

Recommended for use with:

LTW300 series, LTW425, LT300, RCdT300 series, LRCD200 series

**1002-774**

SP5 Switched Probe (1.5m)

Red probe with built in test button to allow you to use both hands while testing.

Recommended for use with:

MFT1700 series, MFT1800 series

**1001-884**

SP4F Switched Probe (1.5m)

Red probe with built in test button to allow you to use both hands while testing.

Recommended for use with:

MFT1500 series, MIT320/330

**6311-089**

SPL1000 Illuminated Switched Probe

Red probe with built in test button to allow you to use both hands while testing. Also has built in torch and is supplied with different sized probe tips.

Recommended for use with:

MFT1500 series, MIT320/330

**1002-490**

Complete set of probes and croc clips for MFT

Includes: Croc clips (red, blue and green), GS38 probe tips (red, blue and green) plus extended probes (red and blue).

Recommended for use with:

1001-991 (3 wire lead set for MFT1700/MFT1800)

1001-975 (Fused 3 wire lead set for MFT1700/MFT1800)

**1002-491**

Complete set of probes and croc clips for MIT

Includes: Croc clips (red, blue and green), GS38 probe tips (red, blue and green) plus extended probes (red and blue).

Recommended for use with:

1002-001 (2 wire lead set for MIT200/300/400)

1002-015 (Fused 2 wire lead set for MIT200/300/400)

**6121-562**

Replacement probe tips for SPL1000

Replacement set of probe tips for the SPL1000 switched probe.

Recommended for use with:

6311-089 (SPL1000 Illuminated Switched Probe for MFT1500 series, MIT320/330)

**1000-215**

ETL30 - 30m extension test lead

1000-217

ETL50 - 50m extension test lead

Green 30m or 50m R2 lead, including green croc clip.

Recommended for use with:

MFT1700 series, MFT1800 series, MFT1500 series, MIT200 series, MIT300 series, MIT400 series

Mains test leads

**6220-810**

SIA10 socket interface adaptor (UK) (1.2m)

Break out lead for testing at standard UK plug sockets. Consists of BS1363 plug separating to three 4mm plugs.

Recommended for use with:

MFT1700 series, MFT1800 series, LTW series

Also compatible with:

MFT1500 series, LRCD200 series, RCDT300 series, LT300, LT310/320/330, MIT200 series, MIT300 series, MIT400 series

**6220-740**

Mains test lead (UK) (1.3m)

BS1363 plug to special 3 pin plug for Megger test equipment.

Recommended for use with:

MFT1500 series, LRCD200 series, RCDT300 series, LT310/320/330, CM400, CM300, LT7

**6231-633**

Mains test lead (UK) (1m)

BS1363 plug to special 5 pin plug for Megger test equipment.

Recommended for use with:

CM500, CM400/2, CM300/2, BMM2000 series, LCB2000 series

**6220-828**

SIA20 socket interface adaptor (AUS) (1.4m)

Break out lead for testing at Australian plug sockets. Consists of AS/NZS 3112 plug separating to three 4mm plugs.

Recommended for use with:

Australian versions of; MFT1700 series, MFT1800 series, LTW series

Also compatible with:

Australian versions of; MFT1500 series, LRCD200 series, RCDT300 series, LT300, LT310/320/330, MIT200 series, MIT300 series, MIT400 series

**2000-674**

SIA45 socket interface adaptor (SCHUKO) (1.4m)

Break out lead for testing at SCHUKO plug sockets. Consists of CEE 7/4 plug separating to three 4mm plugs.

Recommended for use with:

German, French, Spanish and Dutch versions of; MFT1700 series, MFT1800 series, LTW series

Also compatible with:

German, French, Spanish and Dutch versions of; MFT1500 series, LRCD200 series, RCDT300 series, LT300, LT310/320/330, MIT200 series, MIT300 series, MIT400 series

UK

Archcliffe Road Dover
CT17 9EN England
T +44 (0) 1304 502101
F +44 (0) 1304 207342
UKsales@megger.com

UNITED STATES

4271 Bronze Way
Dallas TX 75237-1019 USA
T 800 723 2861 (USA only)
T +1 214 333 3201
F +1 214 331 7399
USsales@megger.com

OTHER TECHNICAL SALES OFFICES

Valley Forge USA, College Station USA, Sydney
AUSTRALIA, Täby SWEDEN, Ontario CANADA,
Trappes FRANCE, Oberursel GERMANY, Aargau
SWITZERLAND, Dubai UAE, Mumbai INDIA,
Johannesburg SOUTH AFRICA, Chonburi
THAILAND, Malaga SPAIN

CERTIFICATION ISO

Registered to ISO 9001:2008 Cert. no. Q 09250
Registered to ISO 14001:2004 Cert. no. EMS 61597

LV_TL_DS_en_V02

www.megger.com
Megger is a registered trademark