



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

RoHS 400-Series 50 Ohm Coaxial Assemblies

400 Series  50 Ohm Impedance	400 Series Low-Loss Cable <ul style="list-style-type: none"> Center Conductor: Copper clad aluminum Shielding: Foil + tinned copper braid Insulation: Physical foam polyethylene Jacket: Polyethylene (Kynar for Plenum Rated) Operating Temperature: -40°C - +80°C 	NOMINAL ATTENUATION			
		MHz	db/100 ft	db/100m	
		900	3.9	12.8	
		1800	5.7	18.6	
		2500	6.8	22.2	
		5800	10.8	35.5	


CA3N002	400-Series Cable, Type N Male / Type N Male, 2.0 ft	19.99	17.99	15.99	13.99	11.99
CA3N010	400-Series Cable, Type N Male / Type N Male, 10.0 ft	24.99	22.49	19.99	17.49	14.99
CA3N020	400-Series Cable, Type N Male / Type N Male, 20.0 ft	29.99	26.99	23.99	20.99	17.99
CA3N025	400-Series Cable, Type N Male / Type N Male, 25.0 ft	34.99	31.49	27.99	24.49	20.99
CA3N030	400-Series Cable, Type N Male / Type N Male, 30.0 ft	54.99	49.49	43.99	38.49	32.99
CA3N040	400-Series Cable, Type N Male / Type N Male, 40.0 ft	64.99	58.49	51.99	45.49	38.99
CA3N050	400-Series Cable, Type N Male / Type N Male, 50.0 ft	47.99	43.19	38.39	33.59	28.79
CA3N075	400-Series Cable, Type N Male / Type N Male, 75.0 ft	87.99	79.19	70.39	61.59	52.79
CA3N100	400-Series Cable, Type N Male / Type N Male, 100.0 ft	119.99	107.99	95.99	83.99	71.99
CA-NMRNMF002	400-Series Cable, Type N Male Right Angle / Type N Male, 2.0 ft	18.99	17.09	15.19	13.29	CALL
CA-NMRNMF010	400-Series Cable, Type N Male Right Angle / Type N Male, 10.0 ft	22.99	20.69	18.39	16.09	CALL
CA-NMRNMF025	400-Series Cable, Type N Male Right Angle / Type N Male, 25.0 ft	34.99	31.49	27.99	24.49	CALL
CA-NMRNMF050	400-Series Cable, Type N Male Right Angle / Type N Male, 50.0 ft	44.99	40.49	35.99	31.49	CALL
CA4NMSM002	400-Series Cable, SMA Male / Type N Male, 2.0 ft	24.99	22.49	19.99	17.49	14.99
CA4NMSM010	400-Series Cable, SMA Male / Type N Male, 10.0 ft	29.99	26.99	23.99	20.99	17.99
CA4NMSM025	400-Series Cable, SMA Male / Type N Male, 25.0 ft	49.99	44.99	39.99	34.99	29.99

RoHS 600-Series 50 Ohm Coaxial Assemblies

600 Series  50 Ohm Impedance	600 Series Low-Loss Bulk Cable <ul style="list-style-type: none"> Center Conductor: Solid copper Shielding: Foil + tinned copper braid Insulation: Physical foam polyethylene Jacket: Polyethylene Operating Temperature: -40°C - +80°C 	NOMINAL ATTENUATION		
		MHz	db/100 ft	db/100m
		900	2.5	8.2
		1800	3.7	12.1
		2500	4.4	14.5
		5800	7.3	23.8

CA-6NMNM010	600-Series Cable, Type N Male / Type N Male, 10.0 ft	52.00	46.80	41.60	36.40	31.20
CA-6NMNM025	600-Series Cable, Type N Male / Type N Male, 25.0 ft	70.00	63.00	56.00	49.00	42.00
CA-6NMNM050	600-Series Cable, Type N Male / Type N Male, 50.0 ft	100.00	92.00	84.00	76.00	68.00
CA-6NMNM075	600-Series Cable, Type N Male / Type N Male, 75.0 ft	130.00	123.50	117.00	110.50	CALL
CA-6NMNM100	600-Series Cable, Type N Male / Type N Male, 100.0 ft	160.00	152.00	144.00	136.00	CALL
CA-6NMNM125	600-Series Cable, Type N Male / Type N Male, 125.0 ft	242.50	218.25	194.00	169.75	145.50
CA-6NMNM150	600-Series Cable, Type N Male / Type N Male, 150.0 ft	220.00	198.00	176.00	154.00	CALL
CA-6NMNM200	600-Series Cable, Type N Male / Type N Male, 200.0 ft	280.00	252.00	224.00	196.00	CALL
CA-6NMNM250	600-Series Cable, Type N Male / Type N Male, 250.0 ft	340.00	306.00	272.00	238.00	CALL
CA-6NMNF025	600-Series Cable, Type N Male / Type N Female, 25.0 ft	70.00	63.00	56.00	49.00	CALL
CA-6NMNF050	600-Series Cable, Type N Male / Type N Female, 50.0 ft	130.00	117.00	104.00	91.00	78.00
CA-6NMNF075	600-Series Cable, Type N Male / Type N Female, 75.0 ft	130.00	117.00	104.00	91.00	CALL
CA-6NMNF100	600-Series Cable, Type N Male / Type N Female, 100.0 ft	160.00	144.00	128.00	112.00	CALL
CA-6NMNF150	600-Series Cable, Type N Male / Type N Female, 150.0 ft	220.00	198.00	176.00	154.00	CALL
CA-6NMNF200	600-Series Cable, Type N Male / Type N Female, 200.0 ft	280.00	252.00	224.00	196.00	CALL
CA-6RTPNM010	600-Series Cable, Reverse Polarity TNC Plug / Type N Male, 10.0 ft	62.00	55.80	49.60	43.40	CALL
CA-6RTPNM025	600-Series Cable, Reverse Polarity TNC Plug / Type N Male, 25.0 ft	70.00	63.00	56.00	49.00	CALL
CA-6RTPNM050	600-Series Cable, Reverse Polarity TNC Plug / Type N Male, 50.0 ft	100.00	90.00	80.00	70.00	CALL
CA-6RTPNM075	600-Series Cable, Reverse Polarity TNC Plug / Type N Male, 75.0 ft	130.00	117.00	104.00	91.00	CALL
CA-6RTPNM100	600-Series Cable, Reverse Polarity TNC Plug / Type N Male, 100.0 ft	205.00	184.50	164.00	143.50	123.00

RoHS 900-Series 50 Ohm Coaxial Assemblies

900 Series  50 Ohm Impedance	900 Series Low-Loss Bulk Cable <ul style="list-style-type: none"> Center Conductor: BC Tube Shielding: Aluminum tape + tinned copper braid Insulation: Foam polyethylene Jacket: Polyethylene Operating Temperature: -40°C - +85°C 	NOMINAL ATTENUATION		
		MHz	db/100 ft	db/100m
		900	1.7	5.6
		1800	2.5	8.2
		2500	2.9	9.8
		5800	4.9	16.0

CA-9NMNF025	900-Series Cable, Type N Male / Type N Female, 25.0 ft	556.00	500.40	444.80	389.20	CALL
CA-9NMNF050	900-Series Cable, Type N Male / Type N Female, 50.0 ft	798.00	718.20	638.40	558.60	CALL
CA-9NMNF075	900-Series Cable, Type N Male / Type N Female, 75.0 ft	1220.00	1098.00	976.00	854.00	CALL
CA-9NMNF100	900-Series Cable, Type N Male / Type N Female, 100.0 ft	1550.00	1395.00	1240.00	1085.00	CALL
CA-9NMNM025	900-Series Cable, Type N Male / Type N Male, 25.0 ft	556.00	500.40	444.80	389.20	CALL
CA-9NMNM050	900-Series Cable, Type N Male / Type N Male, 50.0 ft	798.00	718.20	638.40	558.60	CALL
CA-9NMNM075	900-Series Cable, Type N Male / Type N Male, 75.0 ft	1220.00	1098.00	976.00	854.00	CALL
CA-9NMNM100	900-Series Cable, Type N Male / Type N Male, 100.0 ft	1550.00	1395.00	1240.00	1085.00	CALL

LOW-LOSS CABLES



Did you know...
 L-com offers custom Low Loss cable assemblies? Contact your sales representative for more details.

Same day shipping
 Orders placed before 4:00 EST ship the same day.

