

## MST Hub – Mini DisplayPort to 2x DisplayPort

StarTech ID: MSTMDP122DP



This MST hub lets you connect two monitors to your Mini DisplayPort™ (mDP) 1.2 equipped Windows® tablet, laptop or desktop. It's USB powered, so the only thing you'll need to operate the hub is your computer.

The hub features a newly engineered chipset that was specifically designed and rigorously tested to resolve compatibility issues with the Microsoft Surface™ Pro 3.

### Increase productivity with multiple screens

The newest generations of computers are more portable than ever, which often means that you're left with fewer video outputs and smaller integrated screens. This MST hub solves both of these problems by letting you connect two additional displays to your computer, which makes multitasking much easier.

### Connect to any display

With the MST hub, you can use Mini DisplayPort video adapters and cable adapters that enable you to connect HDMI, VGA or DVI displays. This ensures your MST hub will be compatible with virtually any television, monitor or projector. The hub is VESA and DisplayPort certified to support mDP 1.2 enabled systems, for seamless integration with your existing video equipment.

### Configure your displays for any environment

Using the MST hub, you can extend your desktop onto additional monitors and stream independent content to each display giving you the freedom to multitask and increase your productivity. You can also mirror the same image onto multiple displays for remote viewing applications such as digital signage.

### Enjoy amazing video quality, without draining system resources

MST technology uses your existing video card to minimize the use of system resources while delivering Ultra

HD 4K resolutions. This unprecedented performance makes MST perfect for high-resolution applications such as graphic design, gaming and medical imaging.

*Note: When using a DisplayPort 1.1 video card the MST hub will act as a splitter, automatically mirroring your video source across all displays. Resolution limitations apply.*

The MSTMDP122DP supports plug-and-play installation for a hassle-free setup, and is backed by a StarTech.com 2-year warranty and free lifetime technical support.

*Note: MST shares 10.2 Gbps across all attached displays. Higher resolutions can restrict the available bandwidth with the remaining ports, please see our guideline below for determining an ideal resolution for your setup. Certain graphics adapters have limited MST support and will only output to three displays in total. If more than three monitors are attached the fourth will be disabled.*

Average resolution bandwidth allocation

1920x1080 (High-definition 1080p) @60hz – 22%  
1920x1200 @60hz – 30%  
2560x1440 @60hz – 35%  
2560x1600 @60hz – 38%  
3840 x 2160 (Ultra HD 4K) @30hz – 38%

Note: Exceeding 100% will reduce functionality.

## Applications

- Connect additional displays to your Surface Pro 3
- Use one screen for reference data such as websites, while composing your documents on another screen
- Dock your mDP 1.2 device and add two high-resolution displays at your workstation
- Create a panoramic video wall for DisplayPort digital signage applications
- Edit images, video or audio clips across two additional displays in any orientation or resolution
- Perfect for spanning a spreadsheet or worksheet across two additional displays, to avoid side-scrolling

## Features

- Maximize your productivity by connecting two independent displays to your computer using the MST hub
- Connect to almost any television, monitor or projector with the support of low-cost adapters
- Newly engineered chipset for increased compatibility with Microsoft Surface Pro 3
- Support for resolutions up to 4K
- VESA and DisplayPort certified
- Compatible with DP1.2 graphics cards such as AMD Eyefinity technology and AMD Radeon
- Plug-and-play installation

Technical Specifications

Warranty	2 Years
Audio	Yes
Chipset ID	STDP4320
Converter Type	MST Hub
Output Signal	DisplayPort
Ports	2
Maximum Digital Resolutions	3840x2160 @ 30hz
Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600 3840 x 2160 (Ultra HD 4K) @30hz
Wide Screen Supported	Yes
Connector A	1 - Mini-DisplayPort (20 pin) Male Input
Connector B	2 - DisplayPort (20 pin) Female Output
Color	Black
Enclosure Type	Plastic
Product Height	14 mm [0.6 in]
Product Length	62 mm [2.4 in]
Product Weight	51 g [1.8 oz]
Product Width	58 mm [2.3 in]
Power Source	USB-Powered
Humidity	50-90%
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Shipping (Package) Weight	142 g [5 oz]
Included in Package	1 - 2-port mDP to DP MST Hub
Included in Package	1 - Quick install guide

Certifications, Reports and Compatibility

