

# Doro PhoneEasy® 100w

## Easy to use phone with amplified sound

Perfect easy to use cordless phone with easy to read display and extra clear sound.

- ✓ Large display and easy to read characters
- ✓ Handset volume amplified by up to 30dB
- ✓ Audio boost button



**DORO – WHEN YOU WANT MODERN TELECOM PRODUCTS THAT ARE EASIER TO HEAR, READ, HANDLE AND FEEL MORE SECURE WITH.**

# Doro PhoneEasy® 100w



## Main features

Pre dialling	✓
Speakerphone	✓
Keylock	✓
Call timer	✓
GAP compatible	✓
Maximum number of handsets per base	5
Menu navigation	✓
Range indoor (meters)	50
Range, up to (metres)	300
Key tone	✓
Out of range warning	✓
Clock	✓
Wake up alarm	✓

## Memories

Redial memory	5
One touch memories	2
Two touch memories	9
Phonebook positions	20

## Handset unit display

Backlit display	✓
-----------------	---

## Base unit display

14-segment	✓
------------	---

## Sounds & Signals

Monophonic ringtones:	5
Polyphonic ringtones	5

Ringer volume settings except off	5
Ringer off setting	✓

## Acoustics

Receiving maximum level (dB RLR)	30
Receiving maximum level (dB(A))	30
HAC (hearing aid compatible)	✓
Maximum ringer volume (dB(A) at 1 metre)	90
Microphone mute	✓

## Ergonomic sound™

Volume boost button	+10 dB
---------------------	--------

## Caller ID

Caller ID memory	10
------------------	----

## Ergonomics

Handset size (mm)	180x54x30
-------------------	-----------

## Powering handset unit

Standby time (up to hours)	100
Talk time (up to hours)	10
Battery included (type)	2xAAA NiMH
Low battery warning	✓

## Technology

DECT	✓
PSTN	✓
Eco functionality	✓