



MATERIALS:

Body: Brass, Tarnish Resistant Plating, Center Contact: Gold Plated Beryllium Copper

Mounting Pins: Brass

Dielectric: Teflon per L-P-403

RATINGS:

Operating Voltage: 500 VRMS Max.

Operating Temperature: -65°C (-85°F) to +165°C (+329° F).

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 4788

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA