

PICCOLO ABS B 85 G



Sample photo

Order symbol: ABS B 85 G
Product nbr: 8784304
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074002013
EI. number:
 Finland: 3423453
 Electric No. Denmark: 8212001828
 Electric No. Italy: 7211015
 Electric No. Sweden: 2536704

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	110	80	85	B-3	DIN-35 Mounting rail
inch:	4.3	3.1	3.3	FP 22040	Wall fastening lug (2 pcs)

Materials:	Material:	Rating:
Material:	ABS	Ingress Protection (EN 60529): IP66/IP67
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK07
Cover screws material:	Polyamide	Electrical insulation: Totally insulated
Cover colour:	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour:	Grey	Flammability Rating: UL 94 HB
Gasket material:	Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650
		NEMA Class: NEMA 1, 4, 4X, 6, 6P, 12, 13

Temperatures:	
Temperature °C (short term):	-40 ... 80 °C
Temperature °C (continuous):	-40 ... 60 °C
Temperature °F (short term):	-40 ... 175 °F
Temperature °F (continuous):	-40 ... 140 °F

Accessories:	
B-MP	Mounting plate

