

Data Specification Sheet



KIT16W & KIT16B 10 x Mini LED Ground Light Kit

Code	KIT16W. KIT16B
Description	LED Recessed DIY Kit complete with 10 x 0.2W LED IP65 recessed Luminaires and 12V Driver 1.5mtr cable.
Finishes available	Stainless Steel Blue LED. Stainless Steel White LED
Overall dimensions (mm)	30mm Diameter 28mm length
Cut-out	25mm
Product Weight	1Kg
Recommended product location	Indoor or Outdoor (Not recommended for food preparation areas)
Lamp Supplied	Yes non-replaceable LED
Voltage (V)	230V
Maximum Lamp Wattage (W)	0.2 Watt per ground light
Lumen Output	10 x 15Lm (White) 10 x 4Lm (Blue)
Class	Class III. Must be Earthed
IP	IP65
Distance from lighted object	n/a
Photometric Testing	Not available
Instruction sheet	Yes
Origin of manufacture	China
Main materials:	
• Body & Base	Polycarbonate
• Glass	Polycarbonate
• Bezel	Stainless Steel
Method of fix	Recessed
Lamp type and base	3 x SMD LED
Electrical Connections	Direct fixed cable 2mtr (supplied)
Cable rating (mm SQ /C.S.A.) & type	2core 0.75mm H05RN-F
CE mark	Yes
Quality Assurance System	Yes ISO 9001 QMS
Batch coding details on product	Yes
Certificate of Conformity (Held on File)	Yes
Manufactured in accordance to:	EN60598
Warranty	1 year