


FUSES & FUSEHOLDERS

5x20mm PCB Fuse Carriers

- PCB mounting
- Kinked pin for PCB retention CFH02/W
- Transparent insulation cover CFH02H
- UL94-V0 cover
- Standard according to IEC 127-6 & UL512
- 22.6mm pitch
-  approved


TYPE NO.		SPECIFICATION	
CFH02	Straight pin	Rating	6.3A/ 250V
CFH02/W	Kinked pin	Contacts/Resistance	Tinned, nickel plated Brass
CFH02H	Cover	Moulding	UL94-V1 self extinguishing PPOM
		Dielectric strength	3kV / 60 Sec
		Temperature	-20° to 125°C
		Operating power	1.6W
		Recommended PCB hole size	1.3mm



5x20mm Compact Horizontal & Vertical PCB Mounting Fuseholders

- Finger or screwdriver release, bayonet carrier
- Horizontal or vertical mounting
- Compact footprint 10mm pitch
- Anti solder wicking
- To IEC 127-6 & UL512
-  approved


TYPE NO.		SPECIFICATION	
CFH06	vertical mounting	Rating	6.3A/ 250V
CFH07	horizontal mounting	Contacts/Resistance	Tinned nickel plated Brass, <math><5m\Omega</math>
		Moulding	UL94-V0 flame retardant PBT
		Dielectric strength	3kV / 60"
		Power dissipation	2.5W
		Recommended PCB hole size	1.5mm
		Insulation Resistance	100M Ω



5x20mm PCB Fuse Carriers

- For the PCB mounting of 5x20mm fuses
- Supplied on tape and reel
- Reel size 1000 pcs

TYPE NO.		SPECIFICATION	
CFH01T	Fuse clip	Material	Phosphor bronze, tin plated



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

ENCLOSURES

BATTERIES

TRANS-
FORMERS