

Thermaltake Chaser A31

The newest member of Chaser gaming series, made for gamers to gear with the latest gaming component, offering not only style and personality but an exceptional combination of cooling, performance and expandability for gaming purists to ensure true enjoyment while in or out of the game.

Key Features

- **E-Sport Design** - The black metal meshed highlighted with blue fluorescence stripes on the front panel combined with a windowed side panel, it hard not to get attention on!
- **Handy Top Panel** - Top panel has implemented two of latest data transfer SuperSpeed USB 3.0 ports, a HD microphone and headset jacks, plus a placement platform for users' electronic devices such as USB/drives/mobile/MP3 laying on.
- **Tool-free innovation** - Innovative 5.25" & 3.5" tool-free drive bay design minumized the hassles of installing ODD, HDD and SSD devices.
- **Smart 2 + 1** - Preinstalled two 120mm fans with a back blue LED fan to optimize system ventilation. In order to keep the interior dust free, all intake ventilation holes come with dust protection including a removable dust filter at the bottom of the chassis. Front Intake & Rear Exhaust 120mm fan with Blue LED
- **Convenient Support** - Three retained holes support LCS, four retained holes for advanced cable management ,one large CPU cut-out to ease on CPU cooler installation and removable HDD rack for extra long graphic cards supporting.

Case Specifications

Form Factor:	Midi Tower
Motherboard Support:	ATX, Micro ATX
PSU Support:	Standard ATX
Gaming Case:	Yes
Water Cooling Ready:	Yes
Dimensions:	212mm x 501mm x 495mm (W x H x D)
Packaging Dimensions:	256mm x 576mm x 565mm (W x H x D)
Body Material:	SECC
Front Bezel Material:	Plastic
Side Panel:	Window
External Bays:	3 x 5.25" External 1 x 3.5" External
Internal Bays:	6 x 3.5" Internal 6 x 2.5" Internal
Drive Bay Notes:	
Expansion Slots:	7 x Full Size
Cooling Front:	120 x 120 x 25 mm Turbo fan x 1 (1000rpm, 16dBA)
Cooling Top:	(optional) 120 x 120 x 25 mm fan x 2 or 140 x 140 x 25 mm fan x 2
Cooling Rear:	120 x 120 x 25 mm Blue LED fan (1000rpm,16dBA)
Cooling Side:	None
Cooling Bottom:	(optional) 120 x 120 x 25 mm fan
IO Ports:	2 x USB 3.0 1 x HD Audio (Also Supports AC'97)

	1 x Microphone
Front Bezel Colour:	Black
Body Colour:	Black
System Cabinet Features:	
PSU Included:	No
Net Weight (KGs):	6.5 KGs

General Specifications

Manufacturer Part Number:	VP300A1W2N
EAN Number:	4717964390219
Has Mains Plug:	No
Colour:	Black
What's In The Box:	Case Product Manual
Unit (Product) Dimensions (mm):	212mm x 501mm x 495mm (W x H x D)
Packaging Dimensions (mm):	256mm x 576mm x 565mm (W x H x D)
Net Weight (KGs):	6.5 KGs
Gross Weight (KGs):	8.2 KGs