

Specification	NOTE	PRB-02
Attenuation Ratio	[1]	100:1
Bandwidth		300 MHz
Rise Time		1.16ns
Input Resistance		100M
Input Capacitance		5.5pF
Compensation Range		10 to 30pF
Maximum Voltage		1500Vrms CAT II(2000V DC incl. peak AC)
Working Voltages		1V to 1kV
Device Connection		BNC
Power Requirement		None, Passive
Operating Temperature		0 °C to 50 °C
Humidity		85% RH or less (at 350C)
Safety		Meets EN61010-031 CAT II
Cable Length		1.35M
Compliance		RoHS, CE
Weight	[2]	93 g

FA27K-09

[1] Attenuation ratio is switchable from 1:1 and 10:1 on some models.

[2] Product weight in pack with kit accessories.