

List Price \$2.40 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Ampere Rating	60A
Approvals	UL Listed File: E60616 CCN XCFR2 - CSA Certified File: LR62144 Class 6228 01 - CE Marked
Fingersafe	Yes
Block Material	Nylon
Color	Green
Width	0.35 Inches
Standard Package Size	50
Lug Material	Copper
Maximum Voltage Rating	600VAC
Mounting Type	Track (9080GH/35mm DIN 3)
Recommended End Barrier	GM6B
Terminal Type	Box Lug
Block Type	Standard
Type	GR6
Wire Size	#22 to #8 AWG (Cu)
Density	34 Sections
Depth	1.72 Inches
Height	1.82 Inches

Shipping and Ordering

Category	21702 - Blocks, Terminal, NEMA, Channel Mount, Type G
Discount Schedule	CP5
GTIN	00785901917489
Package Quantity	50
Weight	0.03 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.