



Datasheet for part number DBMM5W5PA101

| |
|---------------------------------------------------------------------------|
| Our Catalog Part Number: DBMM-5W5P-A101 |
| Our Global Manufacturing Part Number: 051522-0151 |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D |

| Product Datasheet | |
|---------------------------------|-----------------------------------------------------------|
| General | Combo D Series: D-Subminiature offering mixed layouts |
| Wire Gauge Range AWG | AWG 8-26 |
| Contact Arrangement | 5W5 (5 empty size 8 cavities) |
| Dielectric Withstanding Voltage | 500 VAC at sea level |
| Current Rating Signal Contacts | 7.5 max |
| Operating Temperature | -55°/+150° |
| Salt Spray Test | 48 hours (96 Hrs for Stainless Steel) |
| Shell Material | Carbon Steel |
| Shell Finish | Cadmium plating |
| Insulator Material | Thermoplastic, type PCT UL 94V-0 |
| Insulator Color | black |
| Gender | Pin |
| Contacts | delivery without size 8 contacts, please order separately |
| Mounting Method | .120" (3,05mm) Through Hole |