

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0002095143**
Status: **Active**
Overview: Standard .093" Pin and Socket Connectors
Description: 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1381, Female, with Gold (Au) Plated Brass Contact, 18-22 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-43660-9999 \(PDF\)](#)

General

| | |
|-------------------------|--|
| Product Family | Crimp Terminals |
| Series | 1381 |
| Application | Power |
| Crimp Quality Equipment | Yes |
| Overview | Standard .093" Pin and Socket Connectors |
| Packaging Alternative | 02-09-5142 (Loose) |
| Product Name | Standard .093" |
| UPC | 800754230094 |

Physical

| | |
|--------------------------------|----------------------|
| Gender | Female |
| Material - Metal | Brass |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Nickel |
| Net Weight | 0.330/g |
| Packaging Type | Reel |
| Plating min - Mating | 0.381µm |
| Plating min - Termination | 0.762µm |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.52-3.05mm |
| Wire Size AWG | 18, 20, 22 |
| Wire Size mm ² | N/A |

Solder Process Data


| | |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

Material Info

| | |
|-----------------|--------------|
| Old Part Number | 1381-A(P550) |
|-----------------|--------------|

Reference - Drawing Numbers

| | |
|-----------------------|---------------|
| Product Specification | PS-43660-9999 |
| Sales Drawing | SD-1381-* |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

1381 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description | Product # |
|--|------------|
| Mini-Mac™ Applicator | 0638927000 |
| Mini-Mac™ Applicator | 0638924000 |
| Extractor Tool for .093 and HCS-125 Product Series | 0638240200 |
| Insertion Tool | 0011020003 |
| Extraction Tool | 0011030006 |
| Terminator Die | 0011402002 |

This document was generated on 06/26/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION