

60468 - CHARGE Buster OVERHEAD IONIZER W/LIGHTS, 3-FAN, 120 VAC



- **Three Fan Steady-State DC Ionization For 2' x 5' Coverage Area**
Neutralizes electrostatic charges on insulators and ungrounded conductors within the coverage area
- **3 Seconds or Less Discharge Time with ± 10 Volts Offset Voltage (Balance)**
Meets the required limits for ionization use in electronics manufacturing areas per ANSI/ESD S20.20 and ESD TR53
- **Two 700 Lumen LED Panel Lights (Cool White)**
Adds additional light to operator work area for improved visibility
- **3 Position Fan Speed: Low, Medium, High**
Ionization performance is consistent at all speeds and allows for use with sensitive applications, such as calibration, test, or repair procedures
- **Sealed Plenum Air Flow**
Prevents contamination from being introduced to workstation
- **Auto-Feedback System (Audible And Visual Alarm Through Single Tri-Color LED)**
Unit will automatically shut down and alarm if/when supply voltage drops
- **120/220 VAC Input Voltage Selectable**
Unit can be used with 110V or 220V power sources
- **Replaceable Emitter Pins**
Field replaceable emitter pins allow for minimal downtime
- **NIST Calibrated**
Calibrated with accepted procedures and standards traceable to the National Institute of Standards and Technology.

West Coast: 3651 Walnut Ave., Chino, CA 91710

East Coast: One Colgate Way, Canton, MA 02021

Tel: (909) 627-8178 | (781) 821-8370

Fax: (909) 627-7449

Email: Service@Desco.com