



ALBUS


LED Under Cabinet Strip Light



Specification:

SE12250 - 250MM - LED Strip Light - 250mm

Wattage: 2.7W
 Voltage: 240V
 LED Qty: 46
 LED Colour: Cool White (6000K)
 Lumen output: 205Lm
 Life Span: 40,000h
 Cable Length: 1m with 13A plug
 240V fitting with integrated on/off switch




Bracket for corner mounting



SE12330 - 330MM - LED Strip Light - 330mm



Wattage: 3.6W
 Voltage: 240V
 LED Qty: 65
 LED Colour: Cool White (6000K)
 Lumen output: 263Lm
 Life Span: 40,000h
 Cable Length: 1m with 13A plug
 240V fitting with integrated on/off switch



Bracket for soffit mounting

SE12550 - 550MM - LED Strip Light - 550mm

Wattage: 6.8W
 Voltage: 240V
 LED Qty: 121
 LED Colour: Cool White (6000K)
 Lumen output: 517Lm
 Life Span: 40,000h
 Cable Length: 1m with 13A plug
 240V fitting with integrated on/off switch



A maximum continuous run of 5 metres can be achieved.

Key Selling Points:

- Fittings can be interlinked for a continuous run of light
- 240V for simple installation
- Available in 3 lengths - 250mm, 330mm & 550mm
- Long lamp life
- Integrated on/off switch (for optional use)
- No U/V & IR emitted from the lamp
- Energy saving, whilst maintaining a high light output
- An ideal energy saving replacement for the T5 strip lights

sensio[®]
 furniture lighting solutions