

CPC Part Number - **MC02382**

Europa Part Number -

HM632.2.230.50

Specifications and dimensions



*Representative image of range

- Hours Run Counter
- Panel mount

Features	
Front height	48mm
Width	48mm
Depth behind panel	32.3mm
Weight	0.046Kg
Ingress protection front	IP65
Ingress protection behind panel	IP20
Counting range	99999.99
Voltage	230V AC 50Hz
Voltage tolerance	± 10%
Current consumption	10ma approx
Ambient temperature	,-30°C to +80°C
Maximum panel thickness	2mm
Maximum panel thickness with retaining clip	10mm
Cut out for mounting	45.2 mm square
Cut out for mounting	50.2 mm round
Related products	
Bezel 55 mm square	C5555
Bezel 72 mm square	C7272

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>