



## Model Name **MX570 Projector**

### Unique selling point

- \* 3200ANSI Lumen High Brightness
- \* 13000:1 High Contrast Ratio
- \* Blu-ray Full HD 3D support
- \* Network Standby <0.5W
- \* SmartEco

### Trade Mark



<b>Projection System</b>	DLP	
<b>Native Resolution</b>	XGA (1024x768)	
<b>Brightness</b>	3200 ANSI Lumen	
<b>Contrast Ratio</b>	13000:1	
<b>Display Color</b>	1.07 Billion Colors	
<b>Lens</b>	F=2.59~2.87, f=16.88~21.88mm	
<b>Aspect Ratio</b>	Native 4:3 (5 aspect ratio selectable)	
<b>Throw Ratio</b>	1.51~1.97 (65"±3% @ 2m)	
<b>Image Size (Diagonal)</b>	60" ~ 300"	
<b>Zoom Ratio</b>	1.3x	
<b>Lamp Type</b>	190W	
<b>Lamp(Normal/Eco/SmartEco/LampSave)*</b>	4500/6000/6500/10000 hours	
<b>Keystone Adjustment</b>	1D, Vertical +/- 40 degrees	
<b>Projection Offset</b>	Vertical: 115% ±5%	
<b>Resolution Support</b>	VGA(640 x 480) to WUXGA_RB(1920 x 1200)*RB = Reduced blanking	
<b>Horizontal Frequency</b>	15K-102KHz	
<b>Vertical Scan Rate</b>	23-120Hz	
<b>Compatibility</b>	HDTV Compatibility	480i, 480p, 576i, 576p, 720p, 1080i, 1080p
	Video Compatibility	NTSC, PAL, SECAM
	3D Compatibility	Frame Sequential: Up to 60Hz 720p
	(Please refer to User Manual for detailed support timing.)	Frame Packing: Up to 24 Hz 1080p
		Side by Side: Up to 24Hz 1080p
		Top Bottom: Up to 60Hz 1080p
<b>Interface</b>	Computer in (D-sub 15pin)	x 2
	HDMI	x 1
	Monitor out	x 1
	Composite Video in (RCA)	x 1
	S-Video in	x 1
	Audio in (Mini Jack)	x 1
	Audio out (Mini Jack)	x 1
	Speaker	10W x 1
	LAN(RJ-45)	x1
	USB (Type mini B)	x1
	RS232 (DB-9pin)	x 1
	IR Receiver	x1 (Front)
<b>Dimensions</b>	Dimensions(W x H x D)	283 x 95 x 222 mm (with feet) 283 x 88.7 x 222 mm (without feet)
	Weight	1.9 Kg (4.19 lbs)
<b>Power</b>	Power Supply	AC100 to 240 V, 50 to 60 Hz
	Power Consumption	Normal 280W, Eco 220W, Standby<0.5W
<b>Audible Noise</b>	33/28 dBA (Normal/Economic mode)	
<b>On-Screen Display Languages</b>	Arabic/Bulgarian/ Croatian/ Czech/ Danish/ Dutch/ English/ Finnish/ French/ German/ Greek/ Hindi/ Hungarian/ Italian/ Indonesian/ Japanese/ Korean/ Norwegian/ Polish/ Portuguese/ Romanian/ Russian/ Simplified Chinese/Spanish/ Swedish/ Turkish/ Thai/ Traditional Chinese (28 Languages)	
<b>Picture Modes</b>	Dynamic / Presentation / sRGB / Cinema / (3D) / User 1 / User 2	
<b>Accessories</b>	<b>Standard</b>	<b>Optional</b>
	Remote Control w Battery	Power Cord (by region)
	User Manual CD	Spare Lamp Kit
	Quick Start Guide	VGA Cable
		Warranty Card (by region)
		Ceiling mount kit
		3D Glasses
		Carry Bag


\*Lamp life results will vary depending on environmental conditions and usage. Actual product's features and specifications are subject to change without notice.

# MX570 Projector

## Distance Chart




The screen aspect ratio is 4:3 and the projected picture is in a 4:3 aspect ratio

Screen size			Distance from screen (mm)			Vertical offset (mm)	
Diagonal		W (mm)	H (mm)	Min length (max. zoom)	Average		Max length (min. zoom)
Inch	mm						
30	762	610	457	920	1061	1201	34
40	1016	813	610	1227	1414	1601	46
50	1270	1016	762	1534	1768	2002	57
60	1524	1219	914	1841	2121	2402	69
80	2032	1626	1219	2455	2829	3202	91
100	2540	2032	1524	3068	3536	4003	114
120	3048	2438	1829	3682	4243	4804	137
150	3810	3048	2286	4602	5304	6005	171
200	5080	4064	3048	6137	7071	8006	229
250	6350	5080	3810	7671	8839	10008	286
300	7620	6096	4572	9205	10607	12009	343




## Ceiling mount Chart

Ceiling Mount screw: M4  
(Max L = 25 mm; Min L = 20 mm)



Unit: mm

## Dimension



Unit: mm