

## G83-6104/G83-6105



Models may vary from the image shown

### Reliable standard keyboard, tried-and-tested a million times over

The CHERRY G83-6000 is the reliable standard keyboard, tried-and-tested a million times over – with soft operation of the keys and completely recyclable.

### Key benefits

- Compact, corded standard keyboard
- Easy to clean keys with scratch-resistant inscriptions
- NTK technology for pleasantly soft operation of the keys
- Uniform switching characteristics (elastomer keys with membrane contact switches)
- 20 million operations for each key
- Can be recycled
- USB or PS/2 connection

### Technical Data:

#### Layout (country or language):

Product dependant, see table "Models"

#### Housing colour:

Product dependant, see table "Models"

#### Key colour:

Product dependant, see table "Models"

#### Weight (product):

662 g

#### Total weight (with packaging):

810 g

#### Cable Length:

approx. 1.75 m

#### Storage Temperature:

-20°C to 60°C

#### Operating Temperature:

0°C to 50°C

#### Current Consumption:

typ. 16 mA

#### Interface:

Product dependant, see table "Models"

#### Product approvals:

- cURus 
- VDE GS 
- c-tick 
- CE 
- FCC 

#### System requirements:

Product dependant, see table "Models"

#### Delivery Volume:

- G83-6104/G83-6105
- Printed instructions

#### Dimensions (product):

approx. 458 x 170 x 42 mm

#### Packaging dimensions:

approx. 493 x 210 x 47 mm

#### Keyboard:

- Key technology: NTK
- Service life, standard key: > 20 million key operations
- Operation characteristics: Soft pressure point
- Inscription technology: Laser
- Inscription layout: Standard
- Number of Keys: Product dependant, see table "Models"

#### Packaging Unit:

- Number of products in the master package: Product dependant, see table "Models"
- Number of master packages per pallet: Product dependant, see table "Models"

#### Warranty:

2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

**Models:**

(possible country/layout versions, others available on request)

Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys	Number of products in the master package	Number of master packages per pallet
G83-6104	G83-6104LPNEU-0	4025112010248	US English with EURO symbol	light grey	light grey	PS/2	PS/2 connection	104	65	2
G83-6104	G83-6104LPNEU-2	4025112011887	US English with EURO symbol	black	black	PS/2	PS/2 connection	104	65	2
G83-6104	G83-6104LPNUS-0	4025112004728	US English	light grey	light grey	PS/2	PS/2 connection	104	65	2
G83-6104	G83-6104LRNEU-0	4025112010248	US English with EURO symbol	light grey	light grey	PS/2	PS/2 connection	104	65	2
G83-6104	G83-6104LRNUS-2	4025112020223	US English	black	black	PS/2	PS/2 connection	104	65	2
G83-6104	G83-6104LUNAR-2	4025112056598	English (US) / Arabic	black	black	USB	USB connection	104	65	2
G83-6104	G83-6104LUNEU-0	4025112010880	US English with EURO symbol	light grey	light grey	USB	USB connection	104	65	2
G83-6104	G83-6104LUNEU-2	4025112028793	US English with EURO symbol	black	black	USB	USB connection	104	65	2
G83-6104	G83-6104LUNRB-2	4025112064692	English (US) / Cyrillic	black	black	USB	USB connection	104	65	2
G83-6105	G83-6105LPNES-2	4025112015236	Spain	black	black	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LPNFR-0	4025112010293	France	light grey	light grey	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LPNGB-0	4025112010699	UK	light grey	light grey	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LPNGB-2	4025112034466	UK	black	black	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LPNRD-0	4025112021220	Germany / Cyrillic	light grey	light grey	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LPQGB-0	4025112020902	UK	light grey	light grey	PS/2	PS/2 connection	105	10	12
G83-6105	G83-6105LPQGB-2	4025112018008	UK	black	black	PS/2	PS/2 connection	105	10	12
G83-6105	G83-6105LRNCH-0	4025112010644	Switzerland	light grey	light grey	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LRNCH-2	4025112036965	Switzerland	black	black	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LRNDE-2	4025112000034	Germany	black	black	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LRNFR-0	4025112010309	France	light grey	light grey	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LRNFR-2	4025112013638	France	black	black	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LRPDE-0	4025112010002	Germany	light grey	light grey	PS/2	PS/2 connection	105	65	2
G83-6105	G83-6105LUNBE-0	4025112010637	Belgium	light grey	light grey	USB	USB connection	105	65	2
G83-6105	G83-6105LUNBE-2	4025112043178	Belgium	black	black	USB	USB connection	105	65	2
G83-6105	G83-6105LUNCH-0	4025112017308	Switzerland	light grey	light grey	USB	USB connection	105	65	2
G83-6105	G83-6105LUNCH-2	4025112047350	Switzerland	black	black	USB	USB connection	105	65	2
G83-6105	G83-6105LUNDE-0	4025112010330	Germany	light grey	light grey	USB	USB connection	105	65	2
G83-6105	G83-6105LUNDE-2	4025112026027	Germany	black	black	USB	USB connection	105	65	2
G83-6105	G83-6105LUNES-0	4025112010613	Spain	light grey	light grey	USB	USB connection	105	65	2
G83-6105	G83-6105LUNES-2	4025112046216	Spain	black	black	USB	USB connection	105	65	2
G83-6105	G83-6105LUNFA-2	4025112067877	French / Arabic	black	black	USB	USB connection	105	65	2
G83-6105	G83-6105LUNFR-0	4025112010347	France	light grey	light grey	USB	USB connection	105	65	2
G83-6105	G83-6105LUNFR-2	4025112028779	France	black	black	USB	USB connection	105	65	2
G83-6105	G83-6105LUNGB-0	4025112010606	UK	light grey	light grey	USB	USB connection	105	65	2
G83-6105	G83-6105LUNGB-2	4025112047336	UK	black	black	USB	USB connection	105	65	2
G83-6105	G83-6105LUNIT-0	4025112010590	Italy	light grey	light grey	USB	USB connection	105	65	2
G83-6105	G83-6105LUNIT-2	4025112046209	Italy	black	black	USB	USB connection	105	65	2
G83-6105	G83-6105LUNNL-0	4025112044717	Netherlands	light grey	light grey	USB	USB connection	105	65	2
G83-6105	G83-6105LUNNL-2	4025112050510	Netherlands	black	black	USB	USB connection	105	65	2

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys	Number of products in the master package	Number of master packages per pallet
40	G83-6105	G83-6105LUNPL-0	4025112052781	Poland	light grey	light grey	USB	USB connection	105	65	2
41	G83-6105	G83-6105LUNPL-2	4025112071959	Poland	black	black	USB	USB connection	105	65	2
42	G83-6105	G83-6105LUNPO-0	4025112047398	Portugal	light grey	light grey	USB	USB connection	105	65	2
43	G83-6105	G83-6105LUNPO-2	4025112047343	Portugal	black	black	USB	USB connection	105	65	2
44	G83-6105	G83-6105LUNRD-0	4025112041990	Germany / Cyrillic	light grey	light grey	USB	USB connection	105	65	2
45	G83-6105	G83-6105LUNRD-2	4025112054082	Germany / Cyrillic	black	black	USB	USB connection	105	65	2
46	G83-6105	G83-6105LUNTS-0	4025112022364	Czech Republic	light grey	light grey	USB	USB connection	105	65	2
47	G83-6105	G83-6105LUNTS-2	4025112040351	Czech Republic	black	black	USB	USB connection	105	65	2
48	G83-6105	G83-6105LUQGB-0	4025112010576	UK	light grey	light grey	USB	USB connection	105	10	12
49	G83-6105	G83-6105LUQGB-2	4025112058004	UK	black	black	USB	USB connection	105	10	12