

45U SmartRack 4-Post Open Frame Rack - Threaded 12-24 Mounting Holes

MODEL NUMBER: SR4POST1224



Highlights

- 45U 4-post open frame rack
- Black steel with threaded (12-24) mounted holes
- Toolless button holes to accept PDUs or cable managers

Package Includes

- SR4POST1224
- Installation hardware
- 50x pieces of 12-24 screws and washers
- Cable management hooks
- Owner's Manual with warranty information

Description

Tripp Lite's 45U 4-Post Open Frame Rack with Threaded Mounting Holes helps IT managers organize their equipment array and provides fast, easy access to installed IT equipment. The SR4POST1224 is a simple solution for housing IT equipment in secure environments and other areas that don't require a lockable rack solution. This 45U rack features heavy-duty cold-rolled steel construction with a black powder-coated finish for durability. It supports stationary loads up to 1000 lb. The SR4POST1224 comes with all the hardware required for assembly and has a self-squaring design with bolt-down provisions. For high-density applications, multiple units can be bolted together side by side.

The open design of the SR4POST1224 provides unobstructed airflow and easy access to equipment and cabling. It has threaded (12-24) mounting holes for easy installation of standard 19-inch rack equipment. The SR4POST1224 supports equipment depths from 22 to 39 inches. This rack also accommodates toolless button-hole mounting for vertical PDUs and cable managers.

Features

- Supports 1000lbs of rackmount equipment
- Adjustable mounting depth (22 to 39 inches)
- Textured powder coat finish
- Heavy-duty cold-rolled steel construction
- Numbered mounting positions
- Bolt down provisions
- Threaded 12-24 holes
- Black finish
- Easy assembly

Specifications

PHYSICAL



| | |
|-------------------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Installed Whole System Maximum Rack Depth (in.) | 39 |
| Installed Whole System Maximum Rack Depth (cm) | 99.06 |
| Installed Whole System Minimum Rack Depth (in.) | 22 |
| Installed Whole System Minimum Rack Depth (cm) | 55.88 |
| Rack Height (U Spaces) | 45 |
| Shipping Dimensions (hwd / in.) | 85 x 6 x 4 |
| Shipping Dimensions (hwd / cm) | 215.9 x 15.24 x 10.16 |
| Shipping Weight (lbs.) | 70 |
| Shipping Weight (kg) | 31.5 |
| Unit Dimensions (hwd / in.) | 84.3 x 20.3 x 22-39.4 |
| Unit Dimensions (hwd / cm) | 214.122 x 51.56 x 55.88 - 100 |
| Unit Weight (lbs.) | 69 |
| Unit Weight (kg) | 31.29 |
| Unit Dimensions (cm) | 214.12 x 51.56 x 55.9~100.1 (depth adjustable) |
| Color | Black |
| Weight Capacity - Stationary (lbs.) | 1000 |
| Weight Capacity - Stationary (kg) | 453.6 |
| Hinged (Swings Away from Wall Bracket) | No |
| SPECIAL FEATURES | |
| Grounding Lug | Includes a set of screws, bolts, and washers to secure a user-supplied grounding wire to Front and Back frames |
| Seismic Rack | No |
| CERTIFICATIONS | |
| NOM (Mexico) | Tested to NOM (Mexico) |
| Approvals | EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com