


SmartRack Roof-Mounted Fan Panel - 6-120V high-performance fans; 630 CFM, 5-15P plug

MODEL NUMBER: SRFANROOF



Highlights

- Roof Mount Fan Panel - 120V
- Ideal for increasing the ventilation of SmartRacks
- Features (6) 120V fans mounted in a roof panel, 6-ft. cord
- Toolless mounting hardware included
- Cold rolled steel with black finish
- 2A current draw

Package Includes

- Fan panel with 6 foot power cord, mounting hardware

Description

Tripp Lite's SmartRack SRFANROOF is ideal for increasing the ventilation in all rack enclosure server cabinets. The unit features(6) 120V high performance fans mounted in a roof panel, 6-ft. cord with NEMA 5-15P input plug, and includes toolless mounting hardware.

COMPATIBLE SMARTRACK ENCLOSURES - [SR25UB](#), [SR25UBKD](#), [SR25UBSP1](#), [SR25UBTAA](#), [SR42UB](#), [SR42UBCL](#), [SR42UBEXP](#), [SR42UBG](#), [SR42UBKD](#), [SR42UBSP1](#), [SR42UBTAA](#), [SR45UB](#), [SR48UB](#), [SR48UBCL](#), [SR48UBEXP](#), [SR48UBSP1](#), [SR42UBTAA](#), and other Tripp Lite SmartRack enclosures that specify the use of this accessory.

Features

- Ideal for increasing the ventilation in all rack enclosure server cabinets
- Unit features(6) 120V high performance fans mounted in a roof panel
- 6-ft. cord with NEMA 5-15P input plug
- Includes toolless mounting hardware
- Compatible SmartRack Enclosures: [SR25UB](#), [SR25UBKD](#), [SR25UBSP1](#), [SR25UBTAA](#), [SR42UB](#), [SR42UBCL](#), [SR42UBEXP](#), [SR42UBG](#), [SR42UBKD](#), [SR42UBSP1](#), [SR42UBTAA](#), [SR45UB](#), [SR48UB](#), [SR48UBCL](#), [SR48UBEXP](#), [SR48UBSP1](#), [SR42UBTAA](#), and other Tripp Lite SmartRack enclosures that specify the use of this accessory

Specifications

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Nominal Input Voltage Description	120V 50/60 Hz
Input Plug Features	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8



USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted ON/OFF rocker switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	3.1 x 23.3 x 37
Shipping Dimensions (hwd / cm)	7.87 x 59.18 x 93.98
Shipping Weight (lbs.)	25
Shipping Weight (kg)	11.34
Unit Dimensions (hwd / in.)	2.1 x 21.9 x 35.5
Unit Dimensions (hwd / cm)	5.33 x 55.63 x 90.17
Unit Weight (lbs.)	22
Unit Weight (kg)	9.98
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>