

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0444761112**
Status: **Active**
Overview: Mini-Fit® Plus HCS
Description: Mini-Fit® HCS Crimp Terminal, 18-20 AWG, Bag, Copper (Cu) Alloy, Tin (Sn)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-44476-001 \(PDF\)](#)

General

Product Family Crimp Terminals
 Series 44476
 Application Power
 Comments High Current
 Crimp Quality Equipment Yes
 Overview Mini-Fit® Plus HCS
 Product Name Mini-Fit®
 UPC 800754367349

Physical

Gender Female
 Material - Metal High Performance Alloy (HPA)
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.200/g
 Packaging Type Bag
 Plating min - Mating 2.540µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.30-3.10mm
 Wire Size AWG 18, 20
 Wire Size mm² N/A


Electrical

Current - Maximum per Contact 11.0A

Material Info

Reference - Drawing Numbers

Product Specification PS-44476-001, RPS-44476-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

China RoHS
Green Image
Not Relevant

Search Parts in this Series

44476 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	0638190900
Extraction Tool	0011030044
Manual Extraction Tool	0638131200