

## Technical Information

Number of Screens 1

Screen Size 54.6 cm  
(21.5")

Screen Mode Full HD

Response Time 5 ms

Aspect Ratio 16:9

Horizontal Viewing Angle 90°

Vertical Viewing Angle 65°

Backlight Technology LED

HDCP Supported Yes

Panel Technology Twisted  
Nematic  
Film (TN  
Film)

Adjustable Display Angle Yes

Tilt Angle -5° to 25°

Swivel Angle No

Adjustable Display Height No

Maximum Adjustable Height No

Adjustable Display Pivot No

## Video

Maximum Resolution 1920 x 1080

Standard Refresh Rate 60 Hz

Colour Support 16.7 Million  
Colours

Contrast Ratio 100,000,000:1

Brightness 200 cd/m<sup>2</sup>

## Interfaces/Ports

DVI Yes

VGA Yes

## Power Description

Input Voltage 110 V AC  
220 V AC

Operating Power Consumption 18.10 W

|  |  |
|--|--|
| Standby Power Consumption              | 450 mW   |
| Off-Mode Power Consumption             | 350 mW   |
| <b>Physical Characteristics</b>        |  |
| VESA Mount Compatible                  | Yes  |
| VESA Mount Standard                    | 100 x 100  |
| Colour                                 | Black  |
| Height                                 | 390.4 mm   |
| Width                                  | 508 mm   |
| Depth                                  | 206.8 mm   |
| Weight (Approximate)                   | 3.24 kg  |
| Weight with Stand (Approximate)        | 3.66 kg  |
| <b>Miscellaneous</b>                   |  |
| Package Contents                       | V226HQL<br>Widescreen<br>LCD Monitor<br>1 x VGA<br>Cable<br>Power Cord |
| Green Compliance Certificate/Authority | ENERGY<br>STAR<br>MPR II   |