

Universal AC Power Adapter Cord, 10A, 18AWG (IEC-320-C14 to NEMA 5-15R), 2-ft.

MODEL NUMBER: P002-002-10A



Highlights

- 2-ft. C14 to 5-15R power cord
- Allows you to plug a power cord with a NEMA 5-15P plug into the IEC-320-C13 outlet of a PDU or UPS.
- Frees up a wall outlet
- 18AWG, SJT, 10A, 125V
- UL Listed

Package Includes

- 2-ft. AC Power Adapter Cord - PC Style (IEC-320-C14) plug to AC Style (NEMA 5-15R) receptacle

Description

Tripp Lite makes your PC installation one step easier. This 2-ft. AC Power Adapter Cord allows you to plug a power cord with a NEMA 5-15P plug into the IEC-320-C13 outlet of a PDU or UPS. Features a NEMA 5-15R receptacle with an IEC-320-C14 plug. UL listed.

Features

- 2-ft. C14 to 5-15R power cord
- Allows you to plug a power cord with a NEMA 5-15P plug into the IEC-320-C13 outlet of a PDU or UPS.
- Frees up a wall outlet
- 18AWG SJT, 10A, 125V
- UL listed

Specifications

INPUT	
Cable Length (ft.)	2
Cable Length (m)	0.61
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	IEC-320-C14
Connector B	NEMA 5-15R



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>